



Main

Range	TeSys
Device short name	GV2ME
Product or component type	Motor starter
Motor starter type	Reversing
Poles description	3P
Utilisation category	AC-3
Motor power kW	7.5 kW at 500 V AC 50/60 Hz 5.5 kW at 400/415 V AC 50/60 Hz 5.5 kW at 440 V AC 50/60 Hz
[Uc] control circuit voltage	24 V AC 50/60 Hz
Thermal protection adjustment range	9...14 A
Magnetic tripping current	170 A

Complementary

Device composition	1 3-pole reversing contactor 1 combination block GV2AF01 1 motor circuit breaker type GV2ME
Coordination type	Type 1
Breaking capacity	I _q = 6 kA at 500 V AC 50/60 Hz conforming to IEC 60947-4-1 I _q = 15 kA at 400/415 V AC 50/60 Hz conforming to IEC 60947-4-1 I _q = 8 kA at 440 V AC 50/60 Hz conforming to IEC 60947-4-1
Product weight	0.46 kg
Height	152 mm
Width	45 mm
Depth	87 mm

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0840 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
