

Product data sheet

Specifications



DOL reversing combination starter - TeSys GV2-ME - 9...14 A - 380...400V AC

GV2ME16K2Q7

❗ Discontinued

Main

Range	TeSys
Device Short Name	GV2ME
Product Or Component Type	Motor starter
Motor Starter Type	Reversing
Poles Description	3P
Utilisation Category	AC-3
Motor Power Kw	5.5 kW at 400/415 V AC 50/60 Hz 5.5 kW at 440 V AC 50/60 Hz 7.5 kW at 500 V AC 50/60 Hz
[Uc] Control Circuit Voltage	380/400 V AC 50/60 Hz
Thermal Protection Adjustment Range	9...14 A
Magnetic Tripping Current	170 A

Complementary

Device Composition	1 3-pole reversing contactor 1 combination block GV2AF01 1 motor circuit breaker type GV2ME
Coordination Type	Type 1
Breaking Capacity	15 kA Iq at 400/415 V AC 50/60 Hz conforming to IEC 60947-4-1 8 kA Iq at 440 V AC 50/60 Hz conforming to IEC 60947-4-1 6 kA Iq at 500 V AC 50/60 Hz conforming to IEC 60947-4-1
Net Weight	0.46 kg
Height	152 mm
Width	45 mm
Depth	87 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications