

Product data sheet

Specifications



enclosed DOL starter TeSys - GVN- GC - 32 A

GVNGC0232

❗ Discontinued

Main

Range Of Product	TeSys
Device Short Name	GVNGC
Motor Starter Type	Non reversing
Product Or Component Type	Enclosed DOL starter
Poles Description	3P
Motor Starter Composition	With circuit breaker
Trip Unit Technology	Magnetic
Thermal Protection Adjustment Range	32 A
Control Type	Rotary handle black
Enclosure Material	Polycarbonate

Complementary

[Ue] Rated Operational Voltage	500 V
Breaking Capacity	100 kA Icu at 220...230 V conforming to IEC 60947-2 15 kA Icu at 500 V conforming to IEC 60947-2 30 kA Icu at 440 V conforming to IEC 60947-2 50 kA Icu at 400...415 V conforming to IEC 60947-2
Cable Entry	2 x 25 mm ISO at top 2 x 25 mm ISO at bottom 2 x 40 mm ISO at bottom 2 x 32 mm ISO at top 2 x 20 mm ISO at top 2 x 40 mm ISO at top 2 x 32 mm ISO at bottom 2 x 20 mm ISO at bottom
Locking Options Description	Padlock in OFF position 1 to 3 padlocks Ø 8
Width	186.3 mm
Height	348 mm
Depth	237 mm
Net Weight	2.45 kg

Environment

Standards	EN 60947 IEC 60947-4 VDE 0660-102 IEC 60439-1
-----------	--

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP407 conforming to IEC 60529
-------------------------	-------------------------------

Contractual warranty

Warranty	18 months
----------	-----------