


Product data sheet

Specifications



Lisse - Switched Socket - 2 gang - 13A DP Stainless Steel with Black Interior

GGBL3020DBSSSG

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range	Lisse
Aesthetic Name	Screwless deco
Product Or Component Type	Switched socket
Device Presentation	Complete product
Outlet Standard	British
Colour Tint	Interior: black Cover plate: stainless steel
Quantity Per Set	Set of 1
Type Of Packing	Bag

Complementary

Switch Function	2-pole
Rated Current	13 A at 250 V AC 50/60 Hz
Actuator	Rocker
Number Of Gangs	2 gangs
Pilot Light	without LED
Fixing Mode	Concealed screws
Connections - Terminals	Screw terminals
Material	Stainless steel
Type Of Installation	Indoor
Depth	36 mm
Width	148 mm
Height	87 mm

Environment

Standards	GSO BS 1363-2
Regulations	GCC
Marking	Gulf Conformity Marking (G-Mark)
Ip Degree Of Protection	IP20

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.8 cm
Package 1 Width	8.7 cm
Package 1 Length	3.6 cm
Package 1 Weight	0.001 g

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information	