

# Product data sheet

Specifications



## Switch disconnector fuse, TeSys GS, 3P, 630A, fuse type DIN, size 3

GS2S3

### Main

Range	TeSys
Product Name	TeSys GS
Device Short Name	GS2S
Product Or Component Type	Switch-disconnector-fuse
Poles Description	3P
Protected Poles Description	3t
Contacts Type And Composition	3 NO
[Ith] Conventional Free Air Thermal Current	630 A (at 40 °C)
[Ie] Rated Operational Current	400 A at 440 V 2 poles in series per phase with terminal covers DC-23A 630 A at 440 V 2 poles in series per phase with terminal covers DC-23B 315 A at 690 V AC-23A 400 A at 690 V AC-23B 500 A at 500 V AC-23A 500 A at 500 V AC-23B 630 A at 400 V AC-23A 630 A at 400 V AC-23B
Fuse Type	DIN
Fuse Size	3
Network Type	AC DC
Network Frequency	50/60 Hz

### Complementary

Type Of Operating Handle	External right side External frontal Direct frontal
Mounting Support	Plate
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	12 kV
Rated Operational Power In W	295 kW at 690 V 355 kW at 400 V 355 kW at 500 V 400 kW at 690 V
Breaking Capacity	60 W
Making Capacity	6300 A at 400 V AC-23B
Breaking Capacity	5040 A at 400 V (AC-23B)
Short-Circuit Withstand	70 kA

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mechanical Durability	8000 cycles
Electrical Durability	1000 cycles AC-23A 1000 cycles AC-23B 200 cycles DC-23A 200 cycles DC-23B
Connections - Terminals	Power circuit: bars63 mm <sup>2</sup> Power circuit: lugs-ring terminals 2 cable(s) 150 mm <sup>2</sup> Power circuit: lugs-ring terminals 2 cable(s) 300 mm <sup>2</sup>
[Icm] Rated Short-Circuit Making Capacity	100 kA at 400 V with protection by gG fuses
Tightening Torque	Power circuit: 44 N.m

## Environment

Standards	IEC 60947-3
Product Certifications	CE
Ip Degree Of Protection	IP20 conforming to IEC 60529 (with terminal cover)
Ambient Air Temperature For Operation	-20...70 °C
Ambient Air Temperature For Storage	-40...80 °C
Fire Resistance	850 °C fuse cover conforming to IEC 60695-2-1 960 °C body conforming to IEC 60695-2-1
Height	300 mm
Width	364 mm
Depth	250 mm
Net Weight	16 kg

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	40.000 cm
Package 1 Width	52.000 cm
Package 1 Length	44.000 cm
Package 1 Weight	16.962 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	2
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	42.424 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>