

Product data sheet

Specifications



Switch, Ultimate Screwless flat plate, 2-pole, screw terminals, IP20, stainless steel

GU2411BSS

Main

Range Of Product	Ultimate
Range	Ultimate
Aesthetic Name	Screwless flat plate
Product Or Component Type	Switch
Switch Function	2-pole
Rated Current	20 AX at 230 V AC

Complementary

Connections - Terminals	Screw terminals
Quantity Per Set	Set of 1
Number Of Gangs	1 gang
Pilot Light	Red neon indicator
Height	88 mm
Width	88 mm

Environment

Standards	BS EN 60669-1
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	9.5 cm
Package 1 Length	9.6 cm
Package 1 Weight	213 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	21.5 cm
Package 2 Width	42.5 cm
Package 2 Length	50 cm
Package 2 Weight	21.861 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 3	PAM
Number Of Units In Package 3	1600
Package 3 Height	102.5 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	369.768 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability


Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Circularity Profile	No need of specific recycling operations