



Main

Range of product	PacDrive 3
Product or component type	Servo motor integrated drive
Device short name	ILM

Complementary

[Us] rated supply voltage	250...700 V
Continuous stall current	4.8 A
Continuous stall torque	12.5 N.m
Peak stall torque	55 N.m
Nominal output power	1910 W
Nominal torque	9.1 N.m
Nominal speed	2000 rpm
Maximum current Irms	24 A
[In] rated current	3.7 A
Shaft end	Keyed
Second shaft	Without second shaft end
Shaft diameter	24 mm
Shaft length	50 mm
Key width	40 mm
Feedback type	Absolute multiturn SinCos Hiperface
Speed feedback resolution	128 periods
Holding brake	Without
Mounting support	International standard flange
Motor flange size	140 mm
Torque constant	2.6 N.m/A at 120 °C
Back emf constant	173 V/krpm at 20 °C
Number of motor poles	10

Rotor inertia	12.68 kg.cm ²
Stator resistance	1.9 Ohm at 20 °C for Ph/Ph 1.32 Ohm at 120 °C for Ph/N
Stator inductance	22 mH at 20 °C for Ph/Ph 11 mH at 120 °C for Ph/N
Maximum radial force Fr	1930 N at 2000 rpm 2430 N at 1000 rpm
Maximum axial force Fa	0.2 x Fr
Type of cooling	Natural convection
Length	309 mm
Number of motor stacks	2
Centring collar diameter	130 mm
Centring collar depth	3.5 mm
Number of mounting holes	4
Mounting holes diameter	11 mm
Circle diameter of the mounting holes	165 mm
Product weight	17.2 kg

Environment

IP degree of protection	IP54
-------------------------	------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1235 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information