



Main

Range of product	TeSys
Device short name	GV2LC
Motor starter type	Non reversing
Product or component type	Enclosed DOL starter
Poles description	3P
Motor starter composition	With circuit breaker
Trip unit technology	Magnetic
Thermal protection adjustment range	10 A
Control type	Rotary handle black
Enclosure material	Polycarbonate

Complementary

[Ue] rated operational voltage	690 V
Breaking capacity	Icu 10 kA at 500 V IEC 60947-2 Icu 100 kA at 220...230 V IEC 60947-2 Icu 100 kA at 400...415 V IEC 60947-2 Icu 20 kA at 440 V IEC 60947-2
Magnetic tripping limit	13 x In +/- 20 %
Cable entry	2 x 20 mm ISO at bottom 2 x 20 mm ISO at top 2 x 25 mm ISO at bottom 2 x 25 mm ISO at top
Locking options description	1 to 3 padlocks Ø 8 Padlock in OFF position
Width	88 mm
Height	166 mm
Depth	173 mm
Product weight	0.78 kg

Environment

Standards	EN 60947 IEC 60439-1 IEC 60947-4 VDE 0660-102
-----------	--

IP degree of protection	IP547 conforming to IEC 60529
-------------------------	-------------------------------

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0841 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

GV2LC0214 is replaced by the following group of products:



Protection components GV2L16

TeSys GV2 - Circuit breaker - magnetic - 14 A - screw clamp terminals
Qty 1



Enclosures GV2PC01

TeSys GV2 - Enclosure for TeSys GV2P/L - black handle - IP65
Qty 1

Reason for Substitution: End of Life | Substitution date: 01 January 2011