



### Main

|                                |             |
|--------------------------------|-------------|
| Range of product               | PROchantier |
| Product or component type      | Cable reel  |
| [Ue] rated operational voltage | 230 V       |
| [In] rated current             | 16 A        |
| Number of power socket outlets | 4           |

### Complementary

|                     |   |
|---------------------|---|
| Safety equipment    | Thermal circuit breaker                   |
| Cable length        | 40 m                                      |
| Cable cross section | 1.5 mm <sup>2</sup>                       |
| Cable stiffness     | Flexible                                  |
| Type of cable       | H07RN-F3G1.5                              |
| Power               | 3600 W unwound cable<br>920 W wound cable |
| Material            | Crosslinked elastomer cable               |
| Colour              | Grey                                      |
| Quantity per set    | Set of 1                                  |
| Height              | 34 cm                                     |
| Width               | 33 cm                                     |
| Depth               | 25 cm                                     |
| Product weight      | 7.5 kg                                    |

### Environment

|                                       |  |
|---------------------------------------|--|
| Standards                             | NF EN 61242                                    |
| IP degree of protection               | IP44 socket-outlet                             |
| Maximum conductor temperature         | 60 °C  |
| Ambient air temperature for operation | -25...53 °C                                    |
| Type of installation                  | Outdoor  |
| Environmental characteristic          | Oil resistant<br>Chemical pollution resistance |
| Environmental health and issues       | Lead free                                      |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

---

|                       |        |
|-----------------------|--------|
| Mechanical robustness | Shocks |
|-----------------------|--------|

---

Offer Sustainability

---

|       |  |
|-------|--|
| REACH | Reference not containing SVHC above the threshold<br>Reference not containing SVHC above the threshold |
|-------|--|

---