


# Product data sheet

Specifications



## Thorsman 50W LED - worklight CH plug

IMT33109

 **Discontinued on:** Sep 6, 2021

 **Discontinued**

### Main

Range	Thorsman
Product Name	Thorsman 50 LED
Product Or Component Type	Work lamp
Light Source	120 x SMD LED 5630 50 W

### Complementary

Type Of Installation	Outdoor Indoor
[Ue] Rated Operational Voltage	100...240 V
Network Type	AC
Network Frequency	50/60 Hz
Plug Pole Configuration	2P + E
Plug Standard	Swiss
Outlet Standard	Swiss
Number Of Power Socket Outlets	2
Luminous Flux	4000 lm
Bulb Lifespan	50000 h
Colour Rendering Index	R <sub>a</sub> =80
Beam Angle	100 °
Cable Insulation Material	Neoprene
Material	TPE (thermoplastic elastomer) ABS (acrylonitrile butadiene-styrene)
Electrical Connection	Power cord H07RN-F3G1.5 3 m
Height	300 mm
Width	305 mm
Depth	117 mm
Net Weight	2.4 kg
Targeted Country	Switzerland

### Environment

Environmental Characteristic	Splashproof Dustproof
------------------------------	--------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP54
Ik Degree Of Protection	IK07
Quality Labels	CE
Ambient Air Temperature For Operation	-25...40 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.5 cm
Package 1 Width	11.7 cm
Package 1 Length	30 cm
Package 1 Weight	2.4 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations