

Product data sheet

Specifications



Thorsman - MMS-P 5x30 - screw - panhead - set of 200

IMT38040

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.

Main

Range Of Product	Thorsman
Product Or Component Type	Screw
Device Short Name	MMS-P
Device Application	Concrete and solid brick materials
Screw Type	Fully threaded
Tool Type	cordless screwdriver
Quantity Per Set	Set of 200

Complementary

Drilling Diameter	4 mm
Screw Diameter	5 mm
Screw Length	30 mm
Shape Of Screw Head	Panhead
Screwdriver Shape	T20
Material	Screw: steel electroplated

Environment

Standards	CE
-----------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.5 cm
Package 1 Width	0.5 cm
Package 1 Length	3 cm
Package 1 Weight	7 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations