



Main

Range	TeSys
Device short name	GV2ME
Product or component type	Motor starter
Motor starter type	Non reversing
Poles description	3P
Utilisation category	AC-3
Motor power kW	1.1 kW at 400/415 V AC 50/60 Hz 1.5 kW at 400/415 V AC 50/60 Hz 1.5 kW at 440 V AC 50/60 Hz 1.5 kW at 500 V AC 50/60 Hz 2.2 kW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	24 V AC 50/60 Hz
Magnetic tripping current	51 A

Complementary

Device composition	1 combination block GV2AF01 1 3-pole contactor 1 motor circuit breaker type GV2ME
Coordination type	Type 1
Thermal protection adjustment range	2.5...4 A
Breaking capacity	I _q = 50 kA at 400/415 V AC 50/60 Hz conforming to IEC 60947-4-1 I _q = 50 kA at 440 V AC 50/60 Hz conforming to IEC 60947-4-1 I _q = 50 kA at 500 V AC 50/60 Hz conforming to IEC 60947-4-1
Product weight	0.46 kg
Height	152 mm
Width	45 mm
Depth	87 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0840 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------