



Main

Range	TeSys
Device short name	GV2ME
Product or component type	Motor starter
Motor starter type	Reversing
Poles description	3P
Utilisation category	AC-3
Motor power kW	1.1 kW at 400/415 V AC 50/60 Hz 1.5 kW at 400/415 V AC 50/60 Hz 1.5 kW at 440 V AC 50/60 Hz 1.5 kW at 500 V AC 50/60 Hz 2.2 kW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	230/240 V AC 50/60 Hz
Thermal protection adjustment range	2.5...4 A
Magnetic tripping current	51 A

Complementary

Device composition	1 motor circuit breaker type GV2ME 1 3-pole reversing contactor 1 combination block GV2AF01
Coordination type	Type 1
Breaking capacity	I _q = 50 kA at 400/415 V AC 50/60 Hz conforming to IEC 60947-4-1 I _q = 50 kA at 440 V AC 50/60 Hz conforming to IEC 60947-4-1 I _q = 50 kA at 500 V AC 50/60 Hz conforming to IEC 60947-4-1
Product weight	0.46 kg
Height	152 mm
Width	45 mm
Depth	87 mm

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0840 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------