



ⓘ Discontinued

GV2ME14K2F7 has not been replaced. Please contact your customer care center for more information.

Main

Range	TeSys
Device short name	GV2ME
Product or component type	Motor starter
Motor starter type	Reversing
Poles description	3P
Utilisation category	AC-3
Motor power kW	3 kW at 400/415 V AC 50/60 Hz 4 kW at 400/415 V AC 50/60 Hz 4 kW at 440 V AC 50/60 Hz 4 kW at 500 V AC 50/60 Hz 5.5 kW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	110 V AC 50/60 Hz
Thermal protection adjustment range	6...10 A
Magnetic tripping current	138 A

Complementary

Device composition	1 3-pole reversing contactor 1 combination block GV2AF01 1 motor circuit breaker type GV2ME
Coordination type	Type 1
Breaking capacity	I _q = 50 kA at 400/415 V AC 50/60 Hz conforming to IEC 60947-4-1 I _q = 6 kA at 500 V AC 50/60 Hz conforming to IEC 60947-4-1 I _q = 15 kA at 440 V AC 50/60 Hz conforming to IEC 60947-4-1
Product weight	0.46 kg
Height	152 mm
Width	45 mm
Depth	87 mm

Offer Sustainability

RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
------------------------	---

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty period	18 months
-----------------	-----------
