



GV2ME16K1V7 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Range	TeSys
Device short name	GV2ME
Product or component type	Motor starter
Motor starter type	Non reversing
Poles description	3P
Utilisation category	AC-3
Motor power kW	7.5 kW at 500 V AC 50/60 Hz 5.5 kW at 400/415 V AC 50/60 Hz 5.5 kW at 440 V AC 50/60 Hz
[Uc] control circuit voltage	400 V AC 50/60 Hz
Magnetic tripping current	170 A

Complementary

Device composition	1 3-pole contactor 1 combination block GV2AF01 1 motor circuit breaker type GV2ME
Coordination type	Type 1
Thermal protection adjustment range	9...14 A
Breaking capacity	I _q = 6 kA at 500 V AC 50/60 Hz conforming to IEC 60947-4-1 I _q = 15 kA at 400/415 V AC 50/60 Hz conforming to IEC 60947-4-1 I _q = 8 kA at 440 V AC 50/60 Hz conforming to IEC 60947-4-1
Product weight	0.46 kg
Height	152 mm
Width	45 mm
Depth	87 mm

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0840 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------