

Product data sheet

Specifications



body for 2-speed motor switch - 3-pole - 60° - 12 A - for Ø 22 mm

K1F002PX

 **Discontinued on:** Jan 29, 2021

 **Discontinued**

Main

| | |
|---------------------------------------------|----------------------------------------|
| Range Of Product | Harmony K |
| Product Or Component Type | Cam switch body |
| Component Name | K1 |
| [Ith] Conventional Free Air Thermal Current | 12 A |
| Sub-Assembly Composition | Contact blocks + fixing plate |
| Cam Switch Function | Pole change switches for 2-speed motor |
| Motor Type | 2 separate windings |
| Off Position | With Off position |
| Switching Positions | Right: 0° - 60° Left: 0° - 300° |
| Product Mounting | Front mounting |
| Fixing Mode | Ø 22 mm hole |
| Bezel Material | Metal |

Complementary

| | |
|----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Switching Angle | 60 ° |
| [Ui] Rated Insulation Voltage | 690 V (pollution degree 3) conforming to IEC 60947-1 |
| [Ithe] Conventional Enclosed Thermal Current | 10 A |
| Rated Operational Power In W | 10500 W AC-21, 500 - 660 V 3 phases conforming to IEC 947-3 1100 W AC-3, 230 V 3 phases conforming to IEC 947-3 1500 W AC-23A, 230 V 3 phases conforming to IEC 947-3 1500 W AC-3, 400 V 1 phase conforming to IEC 947-3 1500 W AC-3, 400 V 3 phases conforming to IEC 947-3 1500 W AC-3, 500 V 3 phases conforming to IEC 947-3 1500 W AC-3, 690 V 3 phases conforming to IEC 947-3 2200 W AC-23A, 400 V 3 phases conforming to IEC 947-3 2200 W AC-23A, 500 V 3 phases conforming to IEC 947-3 2200 W AC-23A, 690 V 3 phases conforming to IEC 947-3 4800 W AC-21, 230 V 3 phases conforming to IEC 947-3 600 W AC-3, 230 V 1 phase conforming to IEC 947-3 8300 W AC-21, 400 V 3 phases conforming to IEC 947-3 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|----------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [Ie] Rated Operational Current Ac | 1 A at 500 V AC-15 conforming to IEC 947-5-1 2 A at 400 V AC-15 conforming to IEC 947-5-1 3 A at 230 V AC-15 conforming to IEC 947-5-1 1.8 A at 690 V AC-3 3 phases conforming to IEC 947-3 2.8 A at 500 V AC-3 3 phases conforming to IEC 947-3 2.8 A at 690 V AC-23A 3 phases conforming to IEC 947-3 3.3 A at 400 V AC-3 3 phases conforming to IEC 947-3 3.8 A at 500 V AC-23A 3 phases conforming to IEC 947-3 4.6 A at 230 V AC-3 3 phases conforming to IEC 947-3 4.8 A at 400 V AC-23A 3 phases conforming to IEC 947-3 5.6 A at 230 V AC-23A 3 phases conforming to IEC 947-3 |
| Electrical Durability | 1000000 cycles AC-15 1000000 cycles AC-21 500000 cycles AC-23 500000 cycles AC-3 |
| Maximum Operating Rate | 2.5 cyc/mn AC-21 2.5 cyc/mn AC-23 2.5 cyc/mn AC-3 8.333 cyc/mn AC-15 |
| Short-Circuit Current | 10000 A |
| Short-Circuit Protection | 16 A cartridge fuse, type gG |
| [Uimp] Rated Impulse Withstand Voltage | 4 kV in isolating function 6 kV conforming to IEC 947-1 |
| Contact Operation | Slow-break |
| Positive Opening | With |
| Electrical Connection | Captive screw clamp terminals flexible, clamping capacity: 2 x 1.5 mm² Captive screw clamp terminals solid, clamping capacity: 1 x 2.5 mm² |
| Mechanical Durability | 1000000 cycles |
| Net Weight | 0.218 kg |

Environment

| | |
|---------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Standards | CENELEC EN 50013 EN 60947-3 for power circuit EN 60947-5-1 for control circuit IEC 60947-3 for power circuit IEC 60947-5-1 for control circuit |
| Product Certifications | CSA 240 V 1 hp 1 phase CSA 240 V 3 hp 3 phases 2 pole(s) UL 240 V 1 hp 3 phases UL 240 V 0.33 hp 1 phase 2 pole(s) |
| Protective Treatment | TC |
| Ambient Air Temperature For Operation | -25...55 °C |
| Ambient Air Temperature For Storage | -40...70 °C |
| Shock Resistance | 30 gn conforming to IEC 68-2-27 |
| Vibration Resistance | 5 gn conforming to IEC 68-2-6 (f = 10...150 Hz) |
| Electrical Shock Protection Class | Class II conforming to IEC 536 Class II conforming to NF C 20-030 |


Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Dimensions Drawings

Body with Metal Base, Secured by Needle Screws


Front Mounting by Ø 22 mm/0.87 in. Hole




a3 75 mm/2.95 in.

Technical Description

Link Positions (Factory Mounted)








Angular Position of Switch



Switching Program

| 300 | 0 | 60 |
|-----|---|----|
| X | | |
| X | | |
| | | |
| | | X |
| | | X |
| | | X |
| | | X |
| X | | |
| | | |
| | | |

Convention Used for Switching Program Representation

-  Contact closed
-  Contact closed in 2 positions and maintained between the 2 positions
-  Sealed assembly for auto-maintain control
-  Overlapping contacts
-  Spring return position: for a switching angle of 90°, spring return is over 30° after the last position (for a maximum of 3 simultaneous contacts).

Example:

