

# Product data sheet

Specifications



## Auxiliary contact block, TeSys Deca, 1NO+1NC, left side mounting

GVAN11

### Main

Range	TeSys TeSys Deca
Device Short Name	GVAN
Product Or Component Type	Auxiliary contact block
Product Compatibility	GV2ME GV2RT GV2L GV3P GV3L GV2LE GV2P
Mounting Location	Left side
Pole Contact Composition	1 NO + 1 NC

### Complementary

[Ui] Rated Insulation Voltage	600 V conforming to UL 508 690 V conforming to IEC 60947-1 600 V conforming to CSA C22.2 No 14
[Ue] Rated Operational Voltage	48...690 V AC 24...240 V DC
[Ith] Conventional Free Air Thermal Current	6 A
Mechanical Durability	100000 cycles
Minimum Switching Current	5 mA
Minimum Switching Voltage	17 V
Protection Type	GB2CB... circuit breaker GG fuse 10 A
Rated Operational Power In Va	300 VA at 48 V AC-15 - electrical durability: 100000 cycles 414 VA at 690 V AC-15 - electrical durability: 100000 cycles 500 VA at 110...127 V AC-15 - electrical durability: 100000 cycles 500 VA at 500 V AC-15 - electrical durability: 100000 cycles 650 VA at 440 V AC-15 - electrical durability: 100000 cycles 720 VA at 230...240 V AC-15 - electrical durability: 100000 cycles 850 VA at 380...415 V AC-15 - electrical durability: 100000 cycles
Rated Operational Power In W	120 W at 240 V DC-13 - electrical durability: 100000 cycles 140 W at 110 V DC-13 - electrical durability: 100000 cycles 140 W at 24 V DC-13 - electrical durability: 100000 cycles 180 W at 60 V DC-13 - electrical durability: 100000 cycles 240 W at 48 V DC-13 - electrical durability: 100000 cycles
Tightening Torque	1.4 N.m - on screw clamp terminals
Height	89 mm
Width	9.3 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	66 mm
Net Weight	0.05 kg
Colour	Dark grey

## Environment

Environmental Characteristic	Normal environment
Product Certifications	UKCA

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	7.000 cm
Package 1 Length	9.000 cm
Package 1 Weight	46.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.500 cm
Package 2 Width	10.000 cm
Package 2 Length	15.200 cm
Package 2 Weight	510.000 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	60
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	3.294 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

Connections and Schema

GVAN11

