



## Main

|                           |                              |
|---------------------------|------------------------------|
| Range of product          | PacDrive 3                   |
| Product or component type | Servo motor integrated drive |
| Device short name         | ILM                          |

## Complementary

|                           |                                       |
|---------------------------|---------------------------------------|
| [Us] rated supply voltage | 250...700 V                           |
| Continuous stall current  | 4.8 A                                 |
| Continuous stall torque   | 12.5 N.m                              |
| Peak stall torque         | 55 N.m                                |
| Nominal output power      | 1910 W                                |
| Nominal torque            | 9.1 N.m                               |
| Nominal speed             | 2000 rpm                              |
| Maximum current Irms      | 24 A                                  |
| [In] rated current        | 3.7 A                                 |
| Shaft end                 | Untapped                              |
| Second shaft              | Without second shaft end              |
| Shaft diameter            | 24 mm                                 |
| Shaft length              | 50 mm                                 |
| Key width                 | 40 mm                                 |
| Feedback type             | Absolute single turn SinCos Hiperface |
| Speed feedback resolution | 128 periods                           |
| Holding brake             | With                                  |
| Holding torque            | 23 N.m (holding brake)                |
| Mounting support          | International standard flange         |
| Motor flange size         | 140 mm                                |
| Torque constant           | 2.6 N.m/A at 120 °C                   |
| Back emf constant         | 173 V/krpm at 20 °C                   |

|                                       |   |
|---------------------------------------|---|
| Number of motor poles                 | 10  |
| Rotor inertia                         | 12.68 kg.cm <sup>2</sup>                                  |
| Stator resistance                     | 1.9 Ohm at 20 °C for Ph/Ph<br>1.32 Ohm at 120 °C for Ph/N |
| Stator inductance                     | 22 mH at 20 °C for Ph/Ph<br>11 mH at 120 °C for Ph/N      |
| Maximum radial force Fr               | 1930 N at 2000 rpm<br>2430 N at 1000 rpm                  |
| Maximum axial force Fa                | 0.2 x Fr  |
| Type of cooling                       | Natural convection  |
| Length                                | 347 mm  |
| Number of motor stacks                | 2   |
| Centring collar diameter              | 130 mm  |
| Centring collar depth                 | 3.5 mm  |
| Number of mounting holes              | 4   |
| Mounting holes diameter               | 11 mm   |
| Circle diameter of the mounting holes | 165 mm  |
| Product weight                        | 18.5 kg   |

## Environment

|                         |      |
|-------------------------|------|
| IP degree of protection | IP65 |
|-------------------------|------|

## Offer Sustainability

|                                  |   |
|----------------------------------|---|
| Sustainable offer status         | Green Premium product   |
| RoHS (date code: YYWW)           | Compliant - since 1235 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product environmental profile    | Available<br><a href="#">Product Environmental Profile</a>  |
| Product end of life instructions | Available<br><a href="#">End of Life Information</a>  |