

# Product data sheet

Specifications



## Fuse connection unit, Vivace, 13A, 250V, white

KB30FSG

### Main

Range	Vivace
Device Short Name	KB30
Product Or Component Type	Fuse connection unit
Device Application	Power supply
Device Presentation	Complete mechanism
Main Colour Tint	White
Colour Tint	Wall: white

### Complementary

Colour Tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting Depth	8 mm
Device Mounting	Surface Flush
Mounting Support	Wall mounted
Fixing Mode	By screw M3.5
Fixing Center	60.3 mm
Embedding Depth	35 mm
Rated Current	13 A at 250 V AC, resistive
Network Frequency	50 Hz
Contacts Material	Brass and phosphor bronze
Connections - Terminals	Pillar terminal
Terminal Identifier	L in L out N in N out Earth
Tightening Torque	0.4 N.m
Clamping Connection Capacity	2 x 4 mm <sup>2</sup> power circuit 3 x 2.5 mm <sup>2</sup> incoming 1 x 1.5 mm <sup>2</sup> outgoing 1 x 2.5 mm <sup>2</sup> input
Width	87 mm
Height	87 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	35 mm
-------	-------

## Environment

Standards	BS 1363-4
Ambient Air Temperature For Operation	-5...40 °C
Ambient Air Temperature For Storage	0...60 °C
Relative Humidity	0...95 %
Operating Altitude	0...2000 m
Environmental Characteristic	Indoor use
Ip Degree Of Protection	IP20

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	3.5 cm
Package 1 Length	14.6 cm
Package 1 Weight	116.9 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	1.239 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	11940 g

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)