


Product data sheet

Specifications



Switch, Vivace, 250V, 16AX, 2 gang,
1 way, white

KB32_1

Main

| | |
|-------------------------------|------------------|
| Range | Vivace |
| Product Or Component Type | Switch |
| Device Short Name | KB32 |
| Device Application | Control |
| Additional Switch Application | On/off switching |
| Number Of Rocker | 2 |
| Switch Function | 1-way |
| Colour Tint | Wall: white |

Complementary

| | |
|--------------------------------|---|
| Technology Type | Electromechanical |
| Device Presentation | Complete product |
| Actuator | Rocker |
| Number Of Gangs | 2 gangs |
| Colour Tint | White |
| Material | Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base |
| Surface Finish | Glossy |
| Surface Treatment | Untreated |
| [Ue] Rated Operational Voltage | 220...250 V |
| Type Of Packing | Plastic bag |
| Network Type | AC |
| Quantity Per Set | 1 |
| Sale Per Indivisible Quantity | 1 |
| Rated Current | 16 AX |
| Projecting Depth | 8 mm |
| Device Mounting | Flush |
| Mounting Support | Wall mounted |
| Fixing Mode | By screw M3.5 |
| Fixing Center | 60.3 mm |
| Connections - Terminals | Screw terminal |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|--------------------------------|--|
| Embedding Depth | 25 mm |
| Number Of Terminals | 4 |
| Rated Current | 16 AX at 250 V AC, inductive 16 AX at 250 V AC, fluorescent 16 AX, resistive |
| [Ue] Rated Operational Voltage | 250 V AC |
| Network Frequency | 50/60 Hz |
| Contacts Material | Brass and phosphor bronze |
| Connections - Terminals | 4 screw terminals |
| Terminal Identifier | L1 L2 COM |
| Tightening Torque | 0.4 N.m |
| Clamping Connection Capacity | <= 2.5 mm² for rigid or stranded cable(s) |
| Wire Stripping Length | 12 mm |
| Width | 86 mm |
| Height | 86 mm |
| Depth | 37 mm |

Environment

| | |
|---------------------------------------|---|
| Standards | IEC 60669-1 MS IEC 60669-1 SS 227 |
| Ambient Air Temperature For Operation | -5...40 °C |
| Relative Humidity | 0...95 % |
| Operating Altitude | 0...2000 m |
| Environmental Characteristic | Indoor use |
| Ip Degree Of Protection | IP20 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Weight | 93.75 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |