

Product data sheet

Specifications



Mureva BOX - junction box - 7 grommets Ø20 - 65x65x45 mm - White

IMT05072

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range Of Product	Mureva
Product Name	Mureva BOX
Product Or Component Type	Junction box
Device Application	Cable installation
Colour Tint	White (RAL 9003)
Quantity Per Set	Set of 5

Complementary

Device Mounting	Surface
Fixing Mode	By screw: body housing
Base Dimension	65 x 45 x 65 mm
Cable Entry	Grommets
Cable Entry Number	7 diameter: 20 mm
Material	ABS (acrylonitrile butadiene-styrene): body PP (polypropylene): cover
Height	65 mm
Width	65 mm
Depth	45 mm

Environment

Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP55
Ik Degree Of Protection	IK07
Glow Wire Temp	650 °C
Standards	EN 60670 CE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.1 cm
Package 1 Width	8.2 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	8.2 cm
Package 1 Weight	68.0 g

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations