

Product data sheet

Specifications



Thorsman 25W LED Arbejdslampe med schuko stik

IMT33089

! Discontinued on: Sep 6, 2021

! Discontinued

Main

Range	Thorsman
Product Name	Thorsman 25 LED
Product Or Component Type	Work lamp
Light Source	COB LED 25 W

Complementary

Type Of Installation	Outdoor Indoor
[Ue] Rated Operational Voltage	100...240 V
Network Type	AC
Network Frequency	50/60 Hz
Plug Pole Configuration	2P + E
Outlet Standard	Schuko/FR
Luminous Flux	2500 lm
Bulb Lifespan	50000 h
Colour Rendering Index	R _a =80
Illuminance	0.5 m: 4400 lux
Cable Insulation Material	Neoprene
Material	Aluminium
Electrical Connection	Power cord H05RN-F3x1.0 5 m
Height	235 mm
Width	220 mm
Depth	75 mm
Net Weight	1.9 kg

Environment

Environmental Characteristic	Dustproof Waterproof
Ip Degree Of Protection	IP67
Ik Degree Of Protection	IK07
Quality Labels	CE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-25...40 °C
---------------------------------------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10 cm
Package 1 Width	22.5 cm
Package 1 Length	24 cm
Package 1 Weight	2.398 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations