

Product data sheet

Specifications

10A TAPOFF UNITS



KBC10DDA20

⚠ Discontinued

Main

Range	Canalis
Product Or Component Type	Tap-off unit
Product Compatibility	KBA KBB KDP
Device Application	Lighting Power socket distribution
Range Compatibility	Canalis KBA busbar trunking Canalis KBB busbar trunking Canalis KDP busbar trunking

Complementary

[Ue] Rated Operational Voltage	230...400 V
[Ui] Rated Insulation Voltage	400 V
[Ie] Rated Operational Current	10 A at 35 °C
Network Frequency	50/60 Hz
Protection Type	Without protection
Busbar Trunking Polarity	L1 + N + PE L2 + L1 + L3 + N + PE L2 + N2 + L3 + N3 + PE
Control Type	Double circuit
Tap-Off Unit Polarity	L1+L2 L2+N L2+N2 L2+L3 L3+N3 L3+N L1+N L1+L3
Tap-Off Unit Connector Type	With phase selection
Standards	EN/IEC 61439-6 EN/IEC 60439-2
Width	127.7 mm
Depth	30 mm
Height	76 mm
Colour	Light grey (RAL 7035)
Net Weight	85 g
Quantity Per Set	Set of 10

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ip Degree Of Protection	IP55 conforming to EN/IEC 60529
-------------------------	---------------------------------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Certifications & Standards

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)