



Main

Range	Thorsman
Product name	Thorsman 18 LED
Product or component type	Work lamp
Light source	SMD LED 5630 18 W

Complementary

Type of installation	Outdoor Indoor
[Ue] rated operational voltage	100...240 V
Network type	AC
Network frequency	50/60 Hz
Plug pole configuration	2P + E
Plug standard	Swiss
Luminous flux	1500 lm
Bulb lifespan	50000 h
Colour rendering index	Ra=80
Colour temperature	4500 K
Beam angle	100 °
Cable insulation material	Neoprene
Material	ABS (acrylonitrile butadiene-styrene) TPE (thermoplastic elastomer)
Electrical connection	2 m H05RN-F2x1.0 mm ² power cord
Electrical insulation class	Class II
Height	200 mm
Width	200 mm
Depth	80 mm
Product weight	0.935 kg

Environment

Environmental characteristic	Dustproof Splashproof
IP degree of protection	IP54

IK degree of protection	IK07
Quality labels	CE
Ambient air temperature for operation	-25...40 °C

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1642 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations