



### Main

Range	Thorsman
Product name	Thorsman 18 LED
Product or component type	Work lamp
Light source	SMD LED 5630 18 W

### Complementary

Type of installation	Outdoor Indoor
[Ue] rated operational voltage	110 V
Network type	AC
Network frequency	50/60 Hz
Plug pole configuration	2P + E
Plug standard	UK
Luminous flux	1500 lm
Bulb lifespan	50000 h
Colour rendering index	Ra=80
Colour temperature	4500 K
Beam angle	100 °
Cable insulation material	Neoprene
Material	ABS (acrylonitrile butadiene-styrene) TPE (thermoplastic elastomer)
Electrical connection	2 m H05RN-F2x1.0 mm <sup>2</sup> power cord
Electrical insulation class	Class II
Height	200 mm
Width	200 mm
Depth	80 mm
Product weight	1.03 kg

### Environment

Environmental characteristic	Dustproof Splashproof
IP degree of protection	IP54

IK degree of protection	IK07
Quality labels	CE
Ambient air temperature for operation	-25...40 °C

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1642 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations