



Main

Range of product	Multifix
Product name	Multifix Eco
Product or component type	Apparatus box
Quantity per set	Set of 25

Complementary

Device mounting	Flush
Device composition	Cover Drilling template Stub with locking tabs of stainless steel
Number of combi-stubs	6 rigid Ø 16 mm / 20 mm combi-stub(s)
Number of gangs	1.5 gangs
Shape	Oval
Colour tint	Grey NCS 3500
Material	PEHD (polyethylene high density)
Distance between supports	60 mm
Diameter	71 mm
Internal depth	55 mm
Length	156 mm
Width	58 mm
Depth	115 mm
Product weight	0.118 kg
Cable cross section	2.5 mm ²

Environment

Standards	IEC 60670-1
Ambient air temperature for operation	-25...90 °C

IP degree of protection	IP40
-------------------------	------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------