

# Product data sheet

Specifications



## OptiLine 50 - switch - 1-pole - white

INS66102

⚠ Discontinued on: Jul 21, 2022

⚠ Discontinued

### Main

Range Of Product	OptiLine 50
Product Type	Switch
Colour	White (RAL 9010)
Quantity Package 1 / Unit	1 piece

### Complementary

Switch Function	1-pole
Number Of Poles	1
Actuator	Rocker
Return	Spring return
Rating	16 A at 250 V AC
Fixing Mode	Snap-fitted
Product Material	PC/ABS
Length	100 mm
Height	50 mm
Width	40 mm

### Environment

Operating Temperature	-5...40 °C
Ip Degree Of Protection	IP20

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	5.8 cm
Package 1 Length	15.6 cm
Package 1 Weight	120 g

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations