

Product data sheet

Specifications



OptiLine 45 - post - one-sided - white - 600 mm

ISM22202

Main

Range Of Product	OptiLine 45
Product Type	Post
Type Of Post	One-sided
Pole/Post Surface Finish	Powder coated

Complementary

Mounting Mode	Free standing
Device Composition	2 x RJ45 connector, communication network category: 6, cable shielding type: S/FTP, 2 modules 6 x socket-outlet, outlet standard:German, 2 modules
Colour	Polar white (RAL 9003)
Fixing Mode	Screw-fixed
Front Opening Size	45 mm
Material	Aluminium
Quantity Package 1 / Unit	1
Height	600 mm
Width	68 mm
Market Segment	Residential Commercial Office
Depth	89 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.0 cm
Package 1 Width	17.0 cm
Package 1 Length	74.0 cm
Package 1 Weight	3.25 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	18
Package 2 Height	63.0 cm
Package 2 Width	80.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	120.0 cm
Package 2 Weight	70.5 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations