

# Product data sheet

Specifications



End feed unit, Canalis KSA250, aluminium, 160/250A, right or left mounting, without line protection, 3L+N+PE, RAL9001

KSA250AB4

## Main

Range Of Product	Canalis
Product Name	KS
Device Short Name	KSA
Product Compatibility	Canalis KSA busbar trunking 100...250 A
Offer Type	Classic Rising main
Product Or Component Type	Feed unit
Conductors Material	Aluminium
[Ie] Rated Operational Current	250 A
[Ue] Rated Operational Voltage	230...690 V
Number Of Circuits	1
Busbar Trunking Polarity	3L + N + PE
Protection Type	Without protection
Control Type	Without
Colour	White (RAL 9001)

## Complementary

Provided Equipment	End cover
Mounting Location	Right Left
Mounting Mode	By screws
Mounting Support	Busbar
Body Material	Metal
Connections - Terminals	Lug for 240 mm² flexible Lug for 240 mm² rigid
Width	501 mm
Depth	173.5 mm
Height	308 mm
Net Weight	8 kg
Standards	IEC 61439-1 IEC 61439-6

## Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.000 cm
Package 1 Width	32.000 cm
Package 1 Length	50.600 cm
Package 1 Weight	9.900 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	6
Package 2 Height	60.000 cm
Package 2 Width	80.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	67.900 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Dimensions Drawings

Dimensions

