



### Main

Range	Canalis
Product name	KR
Product or component type	Busbar trunking
Busbar description	Phase permutation length
Device short name	KRA
Product specific application	Oil and gas Healthcare Real estate and office buildings Mining minerals and metals Water and waste water Enterprise data centres
Device application	Feeder length
Material	Aluminium
[Ie] rated operational current	800 A at 35 °C
Polarity	3L + N + PE
Length	1000 mm

### Complementary

Housing material	Mineral epoxy resin
Contacts material	Tinned aluminium
[Ue] rated operational voltage	1000 V
Network frequency	50/60 Hz
[Ui] rated insulation voltage	1000 V
[Icw] rated short-time withstand current	27 kA
[Ipk] rated peak withstand current	56 kA
Radiated magnetic field	8.79 mT
Thermal stress limit	729 A <sup>2</sup> .s
Voltage drop	With cos φ =1, 0.0166 V at 50 Hz with 1A for 100 m long With cos φ =0.8, 0.016 V at 50 Hz with 1A for 100 m long With cos φ =0.9, 0.0169 V at 50 Hz with 1A for 100 m long With cos φ =0.7, 0.0149 V at 50 Hz with 1A for 100 m long
Mounting location	Indoor Outdoor
Installation direction	Vertical

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

	Horizontal
Marking	Left side : L1 L2 L3 N PE Right side : L3 L2 L1 N PE
Earth conductor	Standard earth
Short-circuit level	Standard version
Product certifications	EAC CE ATEX
Standards	IEC 61439-6
Dimension type	Fix
Width	90 mm
Height	90 mm
Colour	RAL 7030 : grey
Linear load	22 kg/m

## Environment

IP degree of protection	IP68 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Pollution degree	3
Fire resistance	760 °C 180 min conforming to IEC 60331-1
Derating factor	100 % of In at 0...35 °C 84 % of In at 45...50 °C 96 % of In at 35...40 °C 89 % of In at 40...45 °C 78 % of In at 50...55 °C
Operating altitude	98 % of In at 1000 m outdoor 89 % of In at 3000 m outdoor 99 % of In at 2000 m indoor 90 % of In at 4000 m indoor 94 % of In at 2000 m outdoor 83 % of In at 4000 m outdoor 100 % of In at 1000 m indoor 96 % of In at 3000 m indoor
Environmental characteristic	EMC directive conforming to IEC 61439-6 Halogen free

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1606 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>