



Main

Range	Canalis
Product name	KT
Product or component type	Side feeder trunking
Device short name	KTC
Device application	Feeder length
Supply	Dry-type transformer
Material	Copper
[Ie] rated operational current	2000 A at 35 °C
Neutral position	Left
Earth conductor	Reinforced
Short-circuit level	Standard version
Provided equipment	Trunking unit

Complementary

Housing material	Polyester film
Contacts material	Copper
[Ue] rated operational voltage	1000 V
Network frequency	50/60 Hz
[Ui] rated insulation voltage	1000 V
[Icw] rated short-time withstand current	70 kA
[Ipk] rated peak withstand current	154 kA
Radiated magnetic field	0.9 μ T
Thermal stress limit	4900 A ² .s
THDI	15...33 %, maximum load current: 1600 A 0...15 %, maximum load current: 2000 A 33...100 %, maximum load current: 1350 A
Voltage drop	With $\cos \varphi = 1$, 0.0019 V at 50 Hz with 1A for 100 m long With $\cos \varphi = 0.9$, 0.0022 V at 50 Hz with 1A for 100 m long With $\cos \varphi = 0.8$, 0.0022 V at 50 Hz with 1A for 100 m long With $\cos \varphi = 0.7$, 0.0021 V at 50 Hz with 1A for 100 m long
Mounting mode	By screws
Mounting support	Plate
Polarity	3L + N + PE

Number of tap-off outlets	0
Standards	IEC 61439-1 IEC 61439-6
Dimension type	Made to measure
Connection pitch	470...700 mm
Bar width	200 mm
Depth	140 mm
Height	164 mm
Length	1900 mm
Colour	RAL 9001 : white
Linear load	49 kg/m

Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262
Derating factor	100 % of In at 0...35 °C 95 % of In at 35...40 °C 90 % of In at 40...45 °C 84 % of In at 45...50 °C 79 % of In at 50...55 °C

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0949 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product end of life instructions	Need no specific recycling operations