



Main

Range	Canalis
Product name	KT
Product or component type	Expansion unit
Busbar description	Flexible bar
Device short name	KTC
Device application	Feeder length
Material	Copper
[Ie] rated operational current	4000 A at 35 °C
Polarity	3L + N + PE
Number of tap-off outlets	0
Length	1000 mm
Provided equipment	Joining unit Trunking unit

Complementary

Housing material	Polyester film
Contacts material	Copper
[Ue] rated operational voltage	1000 V
Network frequency	50/60 Hz
[Ui] rated insulation voltage	1000 V
[Icw] rated short-time withstand current	90 kA
[Ipk] rated peak withstand current	198 kA
Radiated magnetic field	2.1 µT
Thermal stress limit	8100 A ² .s
THDI	33...100 % 2500 A 15...33 % 3200 A 0...15 % 4000 A
Maximum voltage drop	<0.001 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.0012 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.0012 V with power factor = 0.8 at 50 Hz with 1A for 100 m long

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<0.0012 V with power factor = 0.7 at 50 Hz with 1A for 100 m long

Mounting mode	By hook
Mounting support	Cantilever arm Pendant
Installation direction	Vertical Horizontal
Horizontal distance	30 m
Neutral position	Right
Standards	IEC 61439-1 IEC 61439-6
Dimension type	Fix
Width	140 mm
Height	324 mm
Colour	White (RAL 9001)
Net weight	92 kg
Linear load	92 kg/m

Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262
Derating factor	0...35 °C (100 % of In) 35...40 °C (95 % of In) 40...45 °C (90 % of In) 45...50 °C (84 % of In) 50...55 °C (79 % of In)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins