



Main

Range	Canalis
Product name	KT
Product or component type	Busbar trunking
Busbar description	Distribution length
Device short name	KTC
Tap-off unit compatibility	Bolt-on tap-off unit from Canalis - KT
Device application	High power distribution
Material	Copper
[Ie] rated operational current	4000 A at 35 °C
Polarity	3L + PE
Number of tap-off outlets	2
Nominal output current	400...1250 A
Earth conductor	Standard earth
Short-circuit level	Standard version
Length	4000 mm
Provided equipment	Jointing unit Trunking unit

Complementary

Housing material	Polyester film
Contacts material	Copper
[Ue] rated operational voltage	1000 V
Network frequency	50/60 Hz
[Ui] rated insulation voltage	1000 V
[Icw] rated short-time withstand current	90 kA
[Ipk] rated peak withstand current	198 kA
Electrical connection	Bolted connection
Radiated magnetic field	2.1 µT
Thermal stress limit	8100 A ² .s
THDI	33...100 % 2500 A 15...33 % 3200 A 0...15 % 4000 A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum voltage drop	<0.001 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.0012 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.0012 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.0012 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Mounting mode	By hook
Mounting support	Pendant Cantilever arm
Installation direction	Vertical Horizontal
Neutral position	Right
Tap-off unit interval	2000 mm
Standards	IEC 61439-1 IEC 61439-6
Dimension type	Fix
Width	140 mm
Height	324 mm
Colour	White (RAL 9001)
Net weight	264 kg
Linear load	66 kg/m

Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262
Derating factor	0...35 °C (100 % of In) 35...40 °C (95 % of In) 40...45 °C (90 % of In) 45...50 °C (84 % of In) 50...55 °C (79 % of In)