

Product data sheet

Specifications



C-Bus-6 channel 5A professional dimmer-without RCD-leading edge

L5106D5LP

Main

Range	C-Bus
Product Or Component Type	Dimmer
Device Application	Control
Load Type	Incandescent: 20 W (minimum)
Provided Equipment	RCCB, 2
Number Of Channels	6

Complementary

Maximum Leakage Current	10 mA leading edge 1 mA trailing edge
[Us] Rated Supply Voltage	240 V AC 47...53 Hz 415 V AC 47...53 Hz
Starting Time	0.5 s
Rated Breaking Capacity	6 kA
[Ui] Rated Insulation Voltage	500 V
Net Weight	18 kg
Width	405 mm
Height	451 mm
Depth	115 mm
Maximum Load Current	30 A 1 phase 10 A 3 phases

Environment

Dielectric Strength	2500 V
Directives	2004/108/EC - electromagnetic compatibility
Standards	EN 61000-3-3 EN 61000-3-5 EN 61000-3-2 EN 55015 AS/NZS CISPR 15 IEC 60669-2-1 IEC 60439-1 EN 55014-1 AS/NZS CISPR 14-1 AS/NZS 3439-1 EN 61000-3-11

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	61.8 cm
Package 1 Width	32.2 cm
Package 1 Length	50.5 cm
Package 1 Weight	20.0 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Under investigation
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information