

# Product data sheet

Specifications



## Auxiliary contact block, TeSys K, 4NC, front mounting, screw clamp terminals

LA1KN04

### Main

|   |   |
|---|---|
| Range                                       | TeSys   |
| Product Name                                | TeSys K   |
| Product Or Component Type                   | Auxiliary contact block   |
| Device Short Name                           | LA1   |
| Range Compatibility                         | TeSys K LC1K<br>TeSys K CA2K<br>TeSys K CA3K  |
| Mounting Location                           | Front   |
| Pole Contact Composition                    | 4 NC  |
| Contacts Operation                          | Instantaneous   |
| [Ue] Rated Operational Voltage              | 690 V AC 25...400 Hz  |
| [Ui] Rated Insulation Voltage               | 690 V conforming to IEC 60947-5-1<br>600 V conforming to UL 60947-5-1<br>600 V conforming to CSA C22.2 No 60947-5-1 |
| [Ith] Conventional Free Air Thermal Current | 10 A (at 50 °C)   |
| Standards                                   | EN/IEC 60947-5-1<br>UL 60947-5-1<br>CSA C22.2 No 60947-5-1<br>GB/T 14048.5<br>JIS C8201-5-1                         |
| Product Certifications                      | CB Scheme<br>CCC<br>UL<br>CSA<br>CE<br>UKCA   |

### Complementary

|                               |  |
|-------------------------------|--|
| Irms Rated Making Capacity    | 110 A at <= 690 V AC conforming to IEC 60947 |
| Permissible Short-Time Rating | 80 A 1 s<br>60 A 500 ms<br>110 A 100 ms      |
| Associated Fuse Rating        | 10 A gG at <= 690 V conforming to IEC 60947  |
| Minimum Switching Current     | 5 mA   |
| Minimum Switching Voltage     | 17 V   |
| Non Overlap Distance          | 0.5 mm                                       |
| Insulation Resistance         | > 10 MOhm                                    |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                         |   |
|-------------------------|---|
| Connections - Terminals | Screw clamp terminals 1 cable(s) 0.34...1.5 mm²flexible with cable end              |
|                         | Screw clamp terminals 1 cable(s) 0.75...4 mm²flexible without cable end             |
|                         | Screw clamp terminals 1 cable(s) 1.5...4 mm²rigid                                   |
|                         | Screw clamp terminals 2 cable(s) 0.34...1.5 mm²flexible with cable end              |
|                         | Screw clamp terminals 2 cable(s) 0.75...4 mm²flexible without cable end             |
|                         | Screw clamp terminals 2 cable(s) 1.5...4 mm²rigid                                   |
| Tightening Torque       | 1.3 N.m - with screwdriver Philips No 2<br>1.3 N.m - with screwdriver pozidriv No 2 |
| Height                  | 30 mm   |
| Width                   | 38 mm   |
| Depth                   | 35 mm   |
| Net Weight              | 0.045 kg  |

## Environment

|                                       |                              |
|---------------------------------------|------------------------------|
| Environmental Characteristic          | Normal environment           |
| Ip Degree Of Protection               | IP20 conforming to IEC 60529 |
| Protective Treatment                  | TC conforming to IEC 60068   |
| Ambient Air Temperature For Storage   | -50...80 °C                  |
| Ambient Air Temperature For Operation | -25...50 °C                  |
| Operating Altitude                    | 2000 m                       |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 4 cm     |
| Package 1 Width              | 3.8 cm   |
| Package 1 Length             | 4 cm     |
| Package 1 Weight             | 40 g     |
| Unit Type Of Package 2       | BB1      |
| Number Of Units In Package 2 | 10       |
| Package 2 Height             | 3 cm     |
| Package 2 Width              | 19 cm    |
| Package 2 Length             | 30 cm    |
| Package 2 Weight             | 405 g    |
| Unit Type Of Package 3       | S02      |
| Number Of Units In Package 3 | 100      |
| Package 3 Height             | 15 cm    |
| Package 3 Width              | 30 cm    |
| Package 3 Length             | 40 cm    |
| Package 3 Weight             | 4.535 kg |

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope)                 |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | No need of specific recycling operations  |