


Product data sheet

Specifications



TeSys Deca, suppressor module, RC circuit, 24...48V AC

LA4DA1E

Main

Range	TeSys
Device Short Name	LA4D
Product Or Component Type	Suppressor module
Product Compatibility	3P LC1D80...D150

Complementary

Mounting Mode	By screws
Suppressor Technology	RC circuit
[Uc] Control Circuit Voltage	24...48 V AC 50/60 Hz
Maximum Peak Voltage	3 Uc

Environment

Ambient Air Temperature For Operation	-25...55 °C
Ambient Air Temperature For Storage	-40...80 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	4.2 cm
Package 1 Length	5.1 cm
Package 1 Weight	16.0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	78
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	1.449 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations