



### Main

Range	Canalis
Product name	KR
Product or component type	Long feeder trunking
Device short name	KRA
Product specific application	Water and waste water Enterprise data centres Real estate and office buildings Mining minerals and metals Oil and gas Healthcare
Device application	Feeder length
Supply	Switchboard Oil-immersed transformer
Material	Aluminium
[Ie] rated operational current	4000 A at 35 °C
Busbar/Connection pads direction type	Flat busbar to perpendicular connection pads
Earth conductor	Standard earth
Short-circuit level	Standard version

### Complementary

Housing material	Mineral epoxy resin
Contacts material	Tinned aluminium
[Ue] rated operational voltage	1000 V
Network frequency	50/60 Hz
[Ui] rated insulation voltage	1000 V
[Icw] rated short-time withstand current	100 kA
[Ipk] rated peak withstand current	220 kA
Radiated magnetic field	44.03 mT
Thermal stress limit	10000 A <sup>2</sup> .s
Voltage drop	With cos φ =1, 0.0026 V at 50 Hz with 1A for 100 m long With cos φ =0.9, 0.0043 V at 50 Hz with 1A for 100 m long With cos φ =0.7, 0.005 V at 50 Hz with 1A for 100 m long With cos φ =0.8, 0.0048 V at 50 Hz with 1A for 100 m long
Mounting location	Indoor

	Outdoor
Busbar incoming	Horizontal on side
Polarity	3L + N + PE
Product certifications	ATEX CE EAC
Standards	IEC 61439-6
Dimension type	Made to measure
Colour	RAL 7030 : grey
Linear load	137 kg/m

## Environment

IP degree of protection	IP68 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Pollution degree	3
Fire resistance	760 °C 180 min conforming to IEC 60331-1
Derating factor	100 % of In at 0...35 °C 84 % of In at 45...50 °C 96 % of In at 35...40 °C 89 % of In at 40...45 °C 78 % of In at 50...55 °C
Operating altitude	98 % of In at 1000 m outdoor 89 % of In at 3000 m outdoor 99 % of In at 2000 m indoor 90 % of In at 4000 m indoor 94 % of In at 2000 m outdoor 83 % of In at 4000 m outdoor 100 % of In at 1000 m indoor 96 % of In at 3000 m indoor
Environmental characteristic	EMC directive conforming to IEC 61439-6 Halogen free

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1606 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>