


# Product data sheet

Specifications



Flat zed unit, Canalis KRA,  
aluminium, 5000A, 3L, made to  
measure, grey RAL7030

KRA5000ZP3

## Main

Range	Canalis
Product Name	KR
Product Or Component Type	Zed elbow
Device Short Name	KRA
Product Specific Application	Mining minerals and metals Water and waste water Enterprise data centres Oil and gas Real estate and office buildings Healthcare
Device Application	Change direction
Material	Aluminium
[Ie] Rated Operational Current	5000 A at 35 °C
Polarity	3L
Short-Circuit Level	Standard version

## Complementary

Housing Material	Mineral epoxy resin
Contacts Material	Tinned aluminium
[Ue] Rated Operational Voltage	1000 V
Network Frequency	50/60 Hz
[Ui] Rated Insulation Voltage	1000 V
[Icw] Rated Short-Time Withstand Current	100 kA
[Ipk] Rated Peak Withstand Current	220 kA
Radiated Magnetic Field	58.44 mT
Thermal Stress Limit	10000000 kA².s
Maximum Voltage Drop	<0.0023 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.0038 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.0042 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.0044 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Linear Resistance	L: R20 20 °C= 0.01 mΩ/m L: R1 35 °C= 0.013 mΩ/m at Inc and 50 Hz L: X1 35 °C= 0.023 mΩ/m at Inc and 50 Hz L: Z1 35 °C= 0.026 mΩ/m at Inc and 50 Hz
Mounting Location	Outdoor Indoor

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	EAC CE ATEX
Standards	IEC 61439-6
Width	100 mm
Height	540 mm
Colour	Grey (RAL 7030)
Length	direction 1: 300...700 mm direction 2: 1...700 mm direction 3: 300...700 mm
Linear Load	120 kg/m

## Environment

Ip Degree Of Protection	IP68 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Pollution Degree	3
Fire Resistance	760 °C 180 min conforming to IEC 60331-1
Derating Factor	0...35 °C (100 % of In) 35...40 °C (96 % of In) 40...45 °C (89 % of In) 45...50 °C (84 % of In) 50...55 °C (78 % of In)
Operating Altitude	1000 m 100 % of In (indoor) 2000 m 99 % of In (indoor) 3000 m 96 % of In (indoor) 4000 m 90 % of In (indoor) 1000 m 98 % of In (outdoor) 2000 m 94 % of In (outdoor) 3000 m 89 % of In (outdoor) 4000 m 83 % of In (outdoor)
Environmental Characteristic	EMC directive conforming to IEC 61439-6

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	39.0 cm
Package 1 Width	40.0 cm
Package 1 Length	40.0 cm
Package 1 Weight	151.2 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>