



### Main

Range	TeSys
Product name	TeSys B
Product or component type	Contacteur
Device short name	LC1BR
Contacteur application	Motor-heating-lighting
Utilisation category	AC-1
Control circuit type	AC
Coil type	Standard
Poles description	4P
Pole contact composition	4 NO
[Ie] rated operational current	2750 A (<= 40 °C) AC AC-1 for power circuit
Auxiliary contact composition	2 NO + 2 NC
[Uc] control circuit voltage	127 V AC 50...400 Hz

### Complementary

Protective cover	With
Auxiliary contacts type	Type instantaneous (2 NO + 2 NC)
Control circuit voltage limits	0.4...0.5 U <sub>c</sub> drop-out 0.85...1.1 U <sub>c</sub> operational
[Ui] rated insulation voltage	1000 V - for power circuit - conforming to IEC 60158-1 1000 V - for power circuit - conforming to IEC 60947-4 1500 V - for power circuit - conforming to VDE 0110 group C
Connections - terminals	Power circuit : bars 4 - busbar cross section: 100 x 5 mm
Tightening torque	Power circuit : 35 N.m - on bars
[U <sub>e</sub> ] rated operational voltage	<= 1000 V AC 50/60 Hz for power circuit
[I <sub>th</sub> ] conventional free air thermal current	2750 A at <= 40 °C for power circuit
I <sub>rms</sub> rated making capacity	18000 A at 1000 V AC for power circuit conforming to IEC 60158-1 18000 A at 1000 V AC for power circuit conforming to IEC 60947-4
Rated breaking capacity	11000 A at 660...690 V for power circuit conforming to IEC 60158-1 11000 A at 660...690 V for power circuit conforming to IEC 60947-4 15000 A at 500 V for power circuit conforming to IEC 60158-1 15000 A at 500 V for power circuit conforming to IEC 60947-4 18000 A at 440 V for power circuit conforming to IEC 60158-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

	18000 A at 440 V for power circuit conforming to IEC 60947-4 6000 A at 1000 V for power circuit conforming to IEC 60158-1 6000 A at 1000 V for power circuit conforming to IEC 60947-4
Associated fuse rating	2000 A aM at <= 440 V for power circuit 2400 A gI at <= 440 V for power circuit
Average impedance	0.09 mOhm at 50 Hz - Ith 2750 A for power circuit
Power dissipation per pole	680 W AC-1 - Ith 2750 A
Inrush power in VA	1600 VA
Hold-in power consumption in VA	47 VA
Operating time	100...150 ms closing 20...40 ms opening
Mechanical durability	1200000 cycles
Operating rate	120 cyc/h at <= 55 °C
Rated operational power in VA	3500 VA at 500 V AC-1 - electrical durability: 1000000 cycles - for control circuit 4000 VA at 220 V AC-1 - electrical durability: 1000000 cycles - for control circuit 4000 VA at 380 V AC-1 - electrical durability: 1000000 cycles - for control circuit 2000 VA at 110...127 V AC-1 - electrical durability: 1000000 cycles - for control circuit 4000 VA at 415...440 V AC-1 - electrical durability: 1000000 cycles - for control circuit
Rated operational power in W	200 W at 500 V AC - electrical durability: 1000000 cycles - for control circuit 230 W at 440 V AC - electrical durability: 1000000 cycles - for control circuit 250 W at 110 V AC - electrical durability: 1000000 cycles - for control circuit 250 W at 220 V AC - electrical durability: 1000000 cycles - for control circuit
Height	555 mm
Width	475 mm
Depth	1095 mm
Product weight	52 kg

## Environment

Standards	IEC 60158-1 BS 5424 IEC 60947-4 NF C 63-110 VDE 0660
Product certifications	CSA RINA BV
Protective treatment	TC TH
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-60...80 °C
Operating altitude	3000 m without derating

## Contractual warranty

Warranty period	18 months
-----------------	-----------