


# Product data sheet

Specifications



## TeSys B bar-mounted contactor - 4 poles - AC-1 440V 2750 A- coil 220V AC

LC1BR34M22

 **Discontinued on:** Sep 28, 2021

 **Discontinued**

### Main

Range	TeSys
Product Name	TeSys B
Product Or Component Type	Contactors
Device Short Name	LC1BR
Contactors Application	Motor-heating-lighting
Utilisation Category	AC-1
Control Circuit Type	AC
Coil Type	Standard
Poles Description	4P
Pole Contact Composition	4 NO
[Ie] Rated Operational Current	2750 A (at <40 °C) AC AC-1 for power circuit
Auxiliary Contact Composition	2 NO + 2 NC
[Uc] Control Circuit Voltage	220 V AC 50...400 Hz

### Complementary

Control Circuit Voltage Limits	Drop-out: 0.4...0.5 Uc at 50...400 Hz Operational: 0.85...1.1 Ucw at 50...400 Hz
[Ui] Rated Insulation Voltage	1000 V - for power circuit conforming to IEC 60158-1 1000 V - for power circuit conforming to IEC 60947-4 1500 V - for power circuit conforming to VDE 0110 group C
Mounting Mode	Fixed
Mounting Support	Notched mounting rails Bar support bracket
Connections - Terminals	Power circuit: bolted connection
Tightening Torque	Power circuit: 35 N.m - on bars
[Ue] Rated Operational Voltage	Power circuit: <= 1000 V AC 50/60 Hz
[Ith] Conventional Free Air Thermal Current	2750 A (at 40 °C) for power circuit
Irms Rated Making Capacity	18000 A at 1000 V AC for power circuit conforming to IEC 60158-1 18000 A at 1000 V AC for power circuit conforming to IEC 60947-4

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Rated Breaking Capacity	11000 A at 660...690 V for power circuit conforming to IEC 60158-1 11000 A at 660...690 V for power circuit conforming to IEC 60947-4 15000 A at 500 V for power circuit conforming to IEC 60158-1 15000 A at 500 V for power circuit conforming to IEC 60947-4 18000 A at 440 V for power circuit conforming to IEC 60158-1 18000 A at 440 V for power circuit conforming to IEC 60947-4 6000 A at 1000 V for power circuit conforming to IEC 60158-1 6000 A at 1000 V for power circuit conforming to IEC 60947-4
Associated Fuse Rating	2000 A aM at <= 440 V for power circuit 2400 A gI at <= 440 V for power circuit
Average Impedance	0.09 mOhm - Ith 2750 A 50 Hz for power circuit
Power Dissipation Per Pole	680 W AC-1 - Ith 2750 A
Inrush Power In Va	1600 VA
Hold-In Power Consumption In Va	47 VA 50/60 Hz
Operating Time	100...150 ms closing 50...100 ms opening
Mechanical Durability	1200000 cycles
Maximum Operating Rate	120 cyc/h 55 °C
Height	495 mm
Width	1095 mm
Depth	475 mm
Net Weight	160 kg

## Environment

Standards	NF C 63-110 VDE 0660 IEC 60947-4 IEC 60158-1 BS 5424
Product Certifications	BV RINA CSA
Protective Treatment	TC TH
Ambient Air Temperature For Operation	-5...55 °C
Ambient Air Temperature For Storage	-60...80 °C
Operating Altitude	3000 m without derating

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	58 cm
Package 1 Width	66 cm
Package 1 Length	120 cm
Package 1 Weight	170 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
Eu Rohs Directive	Compliant	<a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>	Product out of China RoHS scope. Substance declaration for your information