



### Main

Range	Canalis
Product name	KR
Product or component type	Busbar trunking
Busbar description	Transport length
Device short name	KRC
Product specific application	Water and waste water Mining minerals and metals Enterprise data centres Oil and gas Real estate and office buildings Healthcare
Device application	Feeder length
Material	Copper
[Ie] rated operational current	2500 A at 35 °C
Polarity	3L + N + PE
Number of tap-off outlets	0
Earth conductor	Standard earth
Short-circuit level	Standard version
Length	1501...2000 mm

### Complementary

Housing material	Mineral epoxy resin
Contacts material	Copper
[Ue] rated operational voltage	1000 V
Network frequency	50/60 Hz
[Ui] rated insulation voltage	1000 V
[Icw] rated short-time withstand current	80 kA
[Ipk] rated peak withstand current	176 kA
Radiated magnetic field	22.1 mT

Thermal stress limit	6400 A <sup>2</sup> .s
Maximum voltage drop	<0.003 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.005 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.006 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.006 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Mounting location	Indoor Outdoor
Installation direction	Horizontal Vertical
Product certifications	CE EAC ATEX
Standards	IEC 61439-6
Dimension type	Made to measure
Width	120 mm
Height	230 mm
Colour	Grey (RAL 7030)
Linear load	105 kg/m

## Environment

IP degree of protection	IP68 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Pollution degree	3
Fire resistance	1000 °C 90 min conforming to DIN 4102-12 2000
Derating factor	0...35 °C (100 % of In) 35...40 °C (96 % of In) 40...45 °C (89 % of In) 45...50 °C (84 % of In) 50...55 °C (78 % of In)
Operating altitude	1000 m 100 % of In (indoor) 2000 m 99 % of In (indoor) 3000 m 96 % of In (indoor) 4000 m 90 % of In (indoor) 1000 m 98 % of In (outdoor) 2000 m 94 % of In (outdoor) 3000 m 89 % of In (outdoor) 4000 m 83 % of In (outdoor)
Environmental characteristic	EMC directive conforming to IEC 61439-6 Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product