


Product data sheet

Specifications



Feed unit for dry type transformers,
Canalis KTA, aluminium, 5000A,
3L+N+PER, made to measure,
neutral N2, white RAL9001

KTA5000EL52

Main

Range	Canalis
Product Name	KT
Product Or Component Type	Side feeder trunking
Device Short Name	KTA
Device Application	Feeder length
Supply	Dry-type transformer
Material	Aluminium
[Ie] Rated Operational Current	5000 A at 35 °C
Neutral Position	Left
Earth Conductor	Reinforced
Short-Circuit Level	Standard version
Provided Equipment	Trunking unit

Complementary

Housing Material	Polyester film
Contacts Material	Copper
[Ue] Rated Operational Voltage	1000 V
Network Frequency	50/60 Hz
[Ui] Rated Insulation Voltage	1000 V
[Icw] Rated Short-Time Withstand Current	120 kA
[Ipk] Rated Peak Withstand Current	264 kA
Radiated Magnetic Field	3.8 µT
Thermal Stress Limit	14400000 kA².s
Thdi	0...15 % 5000 A 15...33 % 4000 A 33...100 % 3200 A
Maximum Voltage Drop	<0.0012 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.00125 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.0012 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.0011 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Mounting Mode	By screws
Mounting Support	Plate
Polarity	3L + N + PER

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Tap-Off Outlets	0
Standards	IEC 61439-1 IEC 61439-6
Dimension Type	Made to measure
Connection Pitch	470...736 mm
Bar Width	200 mm
Depth	140 mm
Height	618 mm
Length	2040 mm
Colour	White (RAL 9001)
Linear Load	72 kg/m

Environment

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Derating Factor	0...35 °C (100 % of In) 35...40 °C (95 % of In) 40...45 °C (90 % of In) 45...50 °C (84 % of In) 50...55 °C (79 % of In)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	34.0 cm
Package 1 Width	62.2 cm
Package 1 Length	190.0 cm
Package 1 Weight	166.8 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information