



## Main

Range	Canalis
Product name	KT
Product or component type	Busbar trunking
Busbar description	Distribution length
Device short name	KTC
Device application	High power distribution
Material	Copper
[Ie] rated operational current	1600 A at 35 °C
Polarity	3L + PE
Number of tap-off outlets	3
Nominal output current	25...630 A
Earth conductor	Standard earth
Short-circuit level	Standard version
Length	2000 mm
Provided equipment	Trunking unit Jointing unit

## Complementary

Housing material	Polyester film
Contacts material	Copper
[Ue] rated operational voltage	1000 V
Network frequency	50/60 Hz
[Ui] rated insulation voltage	1000 V
[Icw] rated short-time withstand current	65 kA
[Ipk] rated peak withstand current	143 kA
Electrical connection	Sliding contact
Radiated magnetic field	0.75 µT
Thermal stress limit	4225 A <sup>2</sup> .s
THDI	0...15 % 1600 A 15...33 % 1350 A 33...100 % 1000 A
Maximum voltage drop	<0.0027 V with power factor = 0.7 at 50 Hz with 1A for 100 m long

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<0.0026 V with power factor = 1 at 50 Hz with 1A for 100 m long  
 <0.0029 V with power factor = 0.9 at 50 Hz with 1A for 100 m long  
 <0.0028 V with power factor = 0.8 at 50 Hz with 1A for 100 m long

Mounting mode	By hook
Mounting support	Pendant Cantilever arm
Installation direction	Vertical Horizontal
Neutral position	Right
Tap-off unit interval	500 mm
Standards	IEC 61439-6 IEC 61439-1
Dimension type	Fix
Width	140 mm
Height	124 mm
Colour	White (RAL 9001)
Net weight	58 kg
Linear load	29 kg/m

## Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262
Derating factor	0...35 °C (100 % of In) 35...40 °C (95 % of In) 40...45 °C (90 % of In) 45...50 °C (84 % of In) 50...55 °C (79 % of In)