



⚠ Discontinued

LC1D1235MD has not been replaced. Please contact your customer care center for more information.

### Main

Range	TeSys
Product name	TeSys D
Product or component type	Contactor
Device short name	LC1D
Contactor application	Resistive load Motor control
Utilisation category	AC-3 AC-1
Poles description	3P
Power pole contact composition	3 NO
[Ue] rated operational voltage	$\leq 300$ V DC for power circuit $\leq 690$ V AC 25...400 Hz for power circuit
[Ie] rated operational current	12 A ( $\leq 60$ °C) at $\leq 440$ V AC AC-3 for power circuit 16 A ( $\leq 60$ °C) at $\leq 440$ V AC AC-1 for power circuit
Motor power kW	3 kW at 220...230 V AC 50/60 Hz 7.5 kW at 500 V AC 50/60 Hz 7.5 kW at 660...690 V AC 50/60 Hz 5.5 kW at 380...400 V AC 50/60 Hz 5.5 kW at 415...440 V AC 50/60 Hz
Motor power HP (UL / CSA)	2 hp at 230/240 V AC 50/60 Hz for 1 phase motors 3 hp at 200/208 V AC 50/60 Hz for 3 phases motors 3 hp at 230/240 V AC 50/60 Hz for 3 phases motors 7.5 hp at 460/480 V AC 50/60 Hz for 3 phases motors 10 hp at 575/600 V AC 50/60 Hz for 3 phases motors 0.5 hp at 115 V AC 50/60 Hz for 1 phase motors
Control circuit type	DC standard
[Uc] control circuit voltage	220 V DC
Auxiliary contact composition	1 NO + 1 NC
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947
Overtoltage category	III
[Ith] conventional free air thermal current	16 A at $\leq 60$ °C for power circuit 10 A at $\leq 60$ °C for signalling circuit
Irms rated making capacity	250 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1
Rated breaking capacity	250 A at 440 V for power circuit conforming to IEC 60947
[Icw] rated short-time withstand current	105 A $\leq 40$ °C 10 s power circuit

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

	210 A <= 40 °C 1 s power circuit 30 A <= 40 °C 10 min power circuit 61 A <= 40 °C 1 min power circuit 100 A 1 s signalling circuit 120 A 500 ms signalling circuit 140 A 100 ms signalling circuit
Associated fuse rating	25 A gG at <= 690 V coordination type 2 for power circuit 40 A gG at <= 690 V coordination type 1 for power circuit 10 A gG for signalling circuit conforming to IEC 60947-5-1
Average impedance	2.5 mOhm at 50 Hz - Ith 16 A for power circuit
[Ui] rated insulation voltage	600 V for power circuit certifications CSA 600 V for power circuit certifications UL 690 V for power circuit conforming to IEC 60947-4-1 690 V for signalling circuit conforming to IEC 60947-1 600 V for signalling circuit certifications CSA 600 V for signalling circuit certifications UL
Electrical durability	2 Mcycles 12 A AC-3 at Ue <= 440 V 0.8 Mcycles 25 A AC-1 at Ue <= 440 V
Power dissipation per pole	0.36 W AC-3 1.56 W AC-1
Safety cover	Without
Mounting support	Rail Plate
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508
Product certifications	DNV LROS (Lloyds register of shipping) GL UL CSA GOST RINA BV CCC
Connections - terminals	Control circuit : spring terminals 1 cable(s) 2.5 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit : spring terminals 2 cable(s) 2.5 mm <sup>2</sup> - cable stiffness: flexible - without cable end Power circuit : spring terminals 1 cable(s) 2.5 mm <sup>2</sup> - cable stiffness: flexible - without cable end Power circuit : spring terminals 2 cable(s) 2.5 mm <sup>2</sup> - cable stiffness: flexible - without cable end
Operating time	53.55...72.45 ms closing 16...24 ms opening
Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical durability	30 Mcycles
Operating rate	3600 cyc/h at <= 60 °C

## Complementary

Coil technology	With integral suppression device
Control circuit voltage limits	0.1...0.25 Uc drop-out at 60 °C, DC 0.7...1.25 Uc operational at 60 °C, DC
Time constant	28 ms
Inrush power in W	5.4 W at 20 °C
Hold-in power consumption in W	5.4 W at 20 °C
Auxiliary contacts type	Type mechanically linked (1 NO + 1 NC) conforming to IEC 60947-5-1 Type mirror contact (1 NC) conforming to IEC 60947-4-1
Signalling circuit frequency	25...400 Hz
Minimum switching current	5 mA for signalling circuit
Minimum switching voltage	17 V for signalling circuit
Non-overlap time	1.5 ms on energisation between NC and NO contact 1.5 ms on de-energisation between NC and NO contact

Insulation resistance	> 10 MOhm for signalling circuit
-----------------------	----------------------------------

## Environment

IP degree of protection	IP20 front face conforming to IEC 60529
Protective treatment	TH conforming to IEC 60068-2-30
Pollution degree	3
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-40...70 °C at Uc
Operating altitude	3000 m without derating
Fire resistance	850 °C conforming to IEC 60695-2-1
Flame retardance	V1 conforming to UL 94
Mechanical robustness	Vibrations contactor open 2 Gn, 5...300 Hz Vibrations contactor closed 4 Gn, 5...300 Hz Shocks contactor open 10 Gn for 11 ms Shocks contactor closed 15 Gn for 11 ms
Height	99 mm
Width	45 mm
Depth	93 mm
Product weight	0.485 kg

## Contractual warranty

Warranty period	18 months
-----------------	-----------