

Product data sheet

Specifications



C-Bus-12 channel 10A architectural dimmer-with 6 RCD-universal

L5112D10UAR6

Main

Range	C-Bus
Product Or Component Type	Dimmer
Device Application	Control
Load Type	Incandescent: 20 W (minimum)
Provided Equipment	RCCB, 2
Number Of Channels	12

Complementary

Maximum Leakage Current	10 mA
[Us] Rated Supply Voltage	240 V AC 47...53 Hz 415 V AC 47...53 Hz
Starting Time	0.5 s
Rated Breaking Capacity	6 kA
[Ui] Rated Insulation Voltage	500 V

Environment

Dielectric Strength	2500 V
Directives	2004/108/EC - electromagnetic compatibility
Standards	AS/NZS CISPR 14-1 IEC 60669-2-1 EN 61000-3-11 IEC 60439-1 EN 55014-1 EN 61000-3-3 EN 55015 AS/NZS CISPR 15 AS/NZS 3439-1 EN 61000-3-2 EN 61000-3-5

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	32.8 cm
Package 1 Width	61.7 cm
Package 1 Length	76.3 cm
Package 1 Weight	15.26 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation
