



Main

| | |
|--|--|
| Range | TeSys |
| Product name | TeSys D |
| Product or component type | Contactor |
| Device short name | LC1D |
| Contactor application | Motor control Resistive load |
| Utilisation category | AC-1 AC-4 AC-3 |
| Poles description | 3P |
| Power pole contact composition | 3 NO |
| [Ue] rated operational voltage | <= 300 V DC for power circuit <= 690 V AC 25...400 Hz for power circuit |
| [Ie] rated operational current | 25 A (<= 60 °C) at <= 440 V AC AC-3 for power circuit 40 A (<= 60 °C) at <= 440 V AC AC-1 for power circuit |
| Motor power kW | 11 kW at 380...400 V AC 50/60 Hz AC-3 15 kW at 500 V AC 50/60 Hz AC-3 15 kW at 660...690 V AC 50/60 Hz AC-3 5.5 kW at 220...230 V AC 50/60 Hz AC-3 11 kW at 415...440 V AC 50/60 Hz AC-3 5.5 kW at 400 V AC 50/60 Hz AC-4 |
| Motor power HP (UL / CSA) | 2 hp at 115 V AC 50/60 Hz for 1 phase motors 7.5 hp at 200/208 V AC 50/60 Hz for 3 phases motors 3 hp at 230/240 V AC 50/60 Hz for 1 phase motors 7.5 hp at 230/240 V AC 50/60 Hz for 3 phases motors 15 hp at 460/480 V AC 50/60 Hz for 3 phases motors 20 hp at 575/600 V AC 50/60 Hz for 3 phases motors |
| Control circuit type | AC 50/60 Hz |
| [Uc] control circuit voltage | 115 V AC 50/60 Hz |
| Auxiliary contact composition | 1 NO + 1 NC |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to IEC 60947 |
| Overvoltage category | III |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|--|--|
| [I _{th}] conventional free air thermal current | 40 A at ≤ 60 °C for power circuit 10 A at ≤ 60 °C for signalling circuit |
| I _{rms} rated making capacity | 450 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 |
| Rated breaking capacity | 450 A at 440 V for power circuit conforming to IEC 60947 |
| [I _{cw}] rated short-time withstand current | 120 A ≤ 40 °C 1 min power circuit 240 A ≤ 40 °C 10 s power circuit 380 A ≤ 40 °C 1 s power circuit 50 A ≤ 40 °C 10 min power circuit 100 A 1 s signalling circuit 120 A 500 ms signalling circuit 140 A 100 ms signalling circuit |
| Associated fuse rating | 40 A gG at ≤ 690 V coordination type 2 for power circuit 63 A gG at ≤ 690 V coordination type 1 for power circuit 10 A gG for signalling circuit conforming to IEC 60947-5-1 |
| Average impedance | 2 mOhm at 50 Hz - I _{th} 40 A for power circuit |
| [U _i] rated insulation voltage | 600 V for power circuit certifications CSA 600 V for power circuit certifications UL 690 V for power circuit conforming to IEC 60947-4-1 690 V for signalling circuit conforming to IEC 60947-1 600 V for signalling circuit certifications CSA 600 V for signalling circuit certifications UL |
| Electrical durability | 1.65 Mcycles 25 A AC-3 at U _e ≤ 440 V 1.4 Mcycles 40 A AC-1 at U _e ≤ 440 V |
| Power dissipation per pole | 3.2 W AC-1 1.25 W AC-3 |
| Safety cover | With |
| Mounting support | Plate Rail |
| Standards | CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 |
| Product certifications | GL GOST LROS (Lloyds register of shipping) DNV CCC RINA CSA UL BV |
| Connections - terminals | Control circuit : lugs-ring terminals - external diameter: 8 mm Power circuit : lugs-ring terminals - external diameter: 10 mm |
| Tightening torque | Control circuit : 1.7 N.m - on lugs-ring terminals - with screwdriver flat Ø 6 mm screw : M3.5 Control circuit : 1.7 N.m - on lugs-ring terminals - with screwdriver Philips No 2 screw : M3.5 Power circuit : 2.5 N.m - on lugs-ring terminals - with screwdriver flat Ø 8 mm screw : M4 Power circuit : 2.5 N.m - on lugs-ring terminals - with screwdriver Philips No 2 screw : M4 |
| Operating time | 4...19 ms opening 12...22 ms closing |
| Safety reliability level | B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1 |
| Mechanical durability | 15 Mcycles |
| Operating rate | 3600 cyc/h at ≤ 60 °C |

Complementary

| | |
|--------------------------------|--|
| Coil technology | Without built-in suppressor module |
| Control circuit voltage limits | 0.3...0.6 U _c drop-out at 60 °C, AC 50/60 Hz 0.8...1.1 U _c operational at 60 °C, AC 50 Hz 0.85...1.1 U _c operational at 60 °C, AC 60 Hz |
| Inrush power in VA | 70 VA at 20 °C (cos φ 0.75) 60 Hz 70 VA at 20 °C (cos φ 0.75) 50 Hz |

| | |
|---------------------------------|--|
| Hold-in power consumption in VA | 7.5 VA at 20 °C (cos ϕ 0.3) 60 Hz 7 VA at 20 °C (cos ϕ 0.3) 50 Hz |
| Heat dissipation | 2...3 W at 50/60 Hz |
| Auxiliary contacts type | Type mechanically linked (1 NO + 1 NC) conforming to IEC 60947-5-1 Type mirror contact (1 NC) conforming to IEC 60947-4-1 |
| Signalling circuit frequency | 25...400 Hz |
| Minimum switching current | 5 mA for signalling circuit |
| Minimum switching voltage | 17 V for signalling circuit |
| Non-overlap time | 1.5 ms on energisation between NC and NO contact 1.5 ms on de-energisation between NC and NO contact |
| Insulation resistance | > 10 MOhm for signalling circuit |

Environment

| | |
|---|---|
| IP degree of protection | IP20 front face conforming to IEC 60529 |
| Protective treatment | TH conforming to IEC 60068-2-30 |
| Pollution degree | 3 |
| Ambient air temperature for operation | -5...60 °C |
| Ambient air temperature for storage | -60...80 °C |
| Permissible ambient air temperature around the device | -40...70 °C at U _c |
| Operating altitude | 3000 m without derating |
| Fire resistance | 850 °C conforming to IEC 60695-2-1 |
| Flame retardance | V1 conforming to UL 94 |
| Mechanical robustness | Vibrations contactor open 2 Gn, 5...300 Hz Vibrations contactor closed 4 Gn, 5...300 Hz Shocks contactor closed 15 Gn for 11 ms Shocks contactor open 8 Gn for 11 ms |
| Height | 85 mm |
| Width | 45 mm |
| Depth | 92 mm |
| Product weight | 0.37 kg |

Offer Sustainability

| | |
|----------------------------------|--|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available Product Environmental Profile |
| Product end of life instructions | Available End of Life Information |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|