



Main

Range	TeSys
Product name	TeSys F
Product or component type	Contactors
Device short name	LC1F
Contactors application	Resistive load
Utilisation category	AC-1
Poles description	4P
Power pole contact composition	4 NO
[Ue] rated operational voltage	≤ 690 V AC 50/60 Hz
[Ie] rated operational current	200 A (≤ 40 °C) at ≤ 440 V AC-1
[Uc] control circuit voltage	24 V DC
Coil type	Standard

Complementary

[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	200 A at ≤ 40 °C
Rated breaking capacity	920 A conforming to IEC 60947-4-1
[Icw] rated short-time withstand current	1100 A ≤ 40 °C 10 s 640 A ≤ 40 °C 30 s 520 A ≤ 40 °C 1 min 400 A ≤ 40 °C 3 min 320 A ≤ 40 °C 10 min
Associated fuse rating	125 A aM at ≤ 440 V 200 A gG at ≤ 440 V
Average impedance	0.37 mOhm at 50 Hz - Ith 200 A
[Ui] rated insulation voltage	1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Power dissipation per pole	15 W AC-1
Mounting support	Plate
Standards	IEC 60947-1 EN 60947-1 JIS C8201-4-1 IEC 60947-4-1 EN 60947-4-1
Product certifications	ABS RMRoS DNV BV CB LROS (Lloyds register of shipping) RINA CCC UL
Connections - terminals	Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² - cable stiffness: flexible - with cable end Power circuit : connector 1 cable(s) 95 mm ² Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: solid - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness: solid - without cable end Power circuit : lugs-ring terminals 1 cable(s) 95 mm ² Power circuit : bolted connection Power circuit : bar 2 x (20 x 3 mm)
Tightening torque	Control circuit : 1.2 N.m Power circuit : 10 N.m
Control circuit voltage limits	0.15...0.2 U _c at 55 °C drop-out 0.85...1.1 U _c at 55 °C operational
Inrush power in W	560 W at 20 °C
Hold-in power consumption in W	4.5 W at 20 °C
Heat dissipation	4.5 W
Operating time	30...40 ms closing 30...50 ms opening
Mechanical durability	10 Mcycles
Operating rate	2400 cyc/h at <= 55 °C

Environment

IP degree of protection	IP2x front face with shrouds (ordered separately) conforming to IEC 60529 IP2x front face with shrouds (ordered separately) conforming to VDE 0106
Protective treatment	TH
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-40...70 °C
Operating altitude	3000 m without derating
Height	162 mm
Width	200.5 mm
Depth	171 mm
Product weight	3.83 kg

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available

Product end of life instructions

Available
[End of Life Information](#)

Contractual warranty

Warranty period

18 months
