

Product data sheet

Specifications



TeSys F contactor - 3P (3 NO) - AC-1 - <= 1000 V 1400 A - coil 120 V AC

LC1F1400G7

ⓘ Discontinued

Main

Range	TeSys
Range Of Product	TeSys F
Product Or Component Type	Contactor
Device Short Name	LC1F
Contactor Application	Resistive load
Utilisation Category	AC-1
Poles Description	3P
[Ue] Rated Operational Voltage	<= 1000 V AC 50/60 Hz <= 460 V DC
[Uc] Control Circuit Voltage	120 V AC 40...400 Hz
[Ie] Rated Operational Current	1400 A (at <40 °C) AC AC-1

Complementary

[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	1400 A (at 40 °C)
Rated Breaking Capacity	2100 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand Current	8000 A 40 °C - 10 s 6000 A 40 °C - 30 s 4500 A 40 °C - 1 min 4000 A 40 °C - 3 min 2600 A 40 °C - 10 min
Associated Fuse Rating	1600 A gG at <= 440 V
Average Impedance	0.1 mOhm - Ith 1700 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C 1000 V conforming to UL 60947-4-1
Power Dissipation Per Pole	150 W AC-1
Overvoltage Category	III
Power Pole Contact Composition	3 NO
Control Circuit Voltage Limits	Operational: 0.85...1.1 Uc 40...400 Hz (at 55 °C) Drop-out: 0.3...0.5 Uc 40...400 Hz (at 55 °C)
Inrush Power In Va	2200 VA, 40...400 Hz cos phi 0.9 (at 20 °C)
Hold-In Power Consumption In Va	36 VA, 40...400 Hz cos phi 0.9 (at 20 °C)
Maximum Operating Rate	600 cyc/h 55 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Operating Time	100...170 ms opening 40...75 ms closing
Connections - Terminals	Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²solid without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm²solid without cable end Power circuit: bar 2 cable(s) - busbar cross section: 100 x 5 mm
Tightening Torque	Control circuit: 1.2 N.m Power circuit: 58 N.m
Mounting Support	Plate
Heat Dissipation	36 W
Standards	IEC 60947-1 EN 60947-4-1 IEC 60947-4-1 JIS C8201-4-1 EN 60947-1 UL 60947-4-1 CSA C22.2 No 60947-4-1
Product Certifications	UL CSA CCC CB Scheme EAC
Compatibility Code	LC1F
Control Circuit Type	AC at 40...400 Hz

Environment

Protective Treatment	TH
Ambient Air Temperature For Operation	-5...40 °C
Ambient Air Temperature For Storage	-60...80 °C
Permissible Ambient Air Temperature Around The Device	-40...60 °C
Height	332 mm
Width	438 mm
Depth	238.6 mm
Operating Altitude	3000 m without derating
Net Weight	29 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration	Product out of China RoHS scope. Substance declaration for your information