

Product data sheet

Specifications



TeSys K contactor , 4P (4 NO) , AC, 1 <= 440 V 20 A , 220...230 V AC coil

LC1K120047M7

ⓘ Discontinued

Main

Range Of Product	TeSys K
Range	TeSys
Product Name	TeSys K
Device Application	Control
Product Or Component Type	Contactors
Device Short Name	LC1K
Utilisation Category	AC-1
Poles Description	4P
Pole Contact Composition	4 NO
[Ie] Rated Operational Current	20 A (at <50 °C) at <= 440 V AC AC-1 for power circuit 16 A (at <70 °C) at 690 V AC AC-1 for power circuit
Signalling Circuit Frequency	<= 400 Hz

Complementary

Contactors Application	Resistive load
Control Circuit Voltage Limits	Operational: 0.85...1.1 Uc (at <50 °C) Drop-out: 0.2...0.75 Uc (at <50 °C)
Control Circuit Type	AC at 50/60 Hz
[Uc] Control Circuit Voltage	220...230 V AC 50/60 Hz
Mechanical Robustness	Shocks contactor closed, on X axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Y axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Z axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on X axis: 6 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Y axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Z axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations contactor closed: 4 Gn, 5...300 Hz conforming to IEC 60068-2-6 Vibrations contactor opened: 2 Gn, 5...300 Hz conforming to IEC 60068-2-6
Standards	EN/IEC 60947-4-1 GB/T 14048.4 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1
Protective Treatment	TC conforming to IEC 60068 TC conforming to DIN 50016
Overvoltage Category	III

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	CB Scheme CCC UL CSA EAC CE UKCA
Operating Altitude	2000 m without derating
[Ith] Conventional Free Air Thermal Current	20 A (at 50 °C) for power circuit
Irms Rated Making Capacity	144 A AC for power circuit conforming to NF C 63-110 144 A AC for power circuit conforming to IEC 60947
Rated Breaking Capacity	110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 70 A at 660...690 V conforming to IEC 60947
Associated Fuse Rating	25 A gG at <= 440 V for power circuit 25 A aM for power circuit
Average Impedance	3 mOhm - Ith 20 A 50 Hz for power circuit
Inrush Power In Va	30 VA (at 20 °C)
Hold-In Power Consumption In Va	4.5 VA (at 20 °C)
Operating Time	10...20 ms coil de-energisation and NO opening 10...20 ms coil energisation and NO closing
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Maximum Operating Rate	3600 cyc/h
Height	58 mm
Width	45 mm
Depth	57 mm
Compatibility Code	LC1K

Environment

Heat Dissipation	1.3 W
Flame Retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------