

Product data sheet

Specifications



TeSys F contactor - 4P (4 NO) - AC-1 - <= 440 V 400 A - coil 24 V DC

LC1F3304BD

⚠ To be discontinued on: Jun 30, 2024

⚠ To be discontinued

Main

| | |
|--------------------------------|---------------------------------------|
| Range | TeSys |
| Range Of Product | TeSys F |
| Product Or Component Type | Contactor |
| Device Short Name | LC1F |
| Contactor Application | Resistive load |
| Utilisation Category | AC-1 |
| Poles Description | 4P |
| [Ue] Rated Operational Voltage | <= 1000 V AC 50/60 Hz <= 460 V DC |
| [Uc] Control Circuit Voltage | 24 V DC |
| [Ie] Rated Operational Current | 400 A (at <40 °C) at <= 440 V AC AC-1 |

Complementary

| | |
|---|---|
| [Uimp] Rated Impulse Withstand Voltage | 8 kV |
| [Ith] Conventional Free Air Thermal Current | 400 A (at 40 °C) |
| Rated Breaking Capacity | 2640 A conforming to IEC 60947-4-1 |
| [Icw] Rated Short-Time Withstand Current | 2650 A 40 °C - 10 s 1800 A 40 °C - 30 s 1300 A 40 °C - 1 min 900 A 40 °C - 3 min 750 A 40 °C - 10 min |
| Associated Fuse Rating | 400 A aM at <= 440 V 500 A gG at <= 440 V |
| Average Impedance | 0.28 mOhm - Ith 400 A 50 Hz |
| [Ui] Rated Insulation Voltage | 1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C |
| Power Dissipation Per Pole | 44 W AC-1 |
| Overvoltage Category | III |
| Power Pole Contact Composition | 4 NO |
| Control Circuit Voltage Limits | Operational: 0.85...1.1 Uc (at 55 °C) Drop-out: 0.15...0.2 Uc (at 55 °C) |
| Mechanical Durability | 10 Mcycles |
| Inrush Power In W | 750 W (at 20 °C) |
| Hold-In Power Consumption In W | 5 W at 20 °C |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------------|--|
| Maximum Operating Rate | 2400 cyc/h 55 °C |
| Operating Time | 40...50 ms closing 40...65 ms opening |
| Connections - Terminals | Control circuit: screw clamp terminals 1 cable(s) 1...4 mm ² flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm ² flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm ² flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm ² solid without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm ² solid without cable end Power circuit: lugs-ring terminals 1 cable(s) 240 mm ² Power circuit: bar 2 cable(s) - busbar cross section: 30 x 5 mm Power circuit: bolted connection |
| Tightening Torque | Control circuit: 1.2 N.m Power circuit: 35 N.m |
| Mounting Support | Plate |
| Heat Dissipation | 5 W |
| Standards | EN 60947-4-1 EN 60947-1 IEC 60947-1 JIS C8201-4-1 IEC 60947-4-1 |
| Product Certifications | BV RINA CCC CB RMRoS LROS (Lloyds register of shipping) DNV ABS UL UKCA |
| Compatibility Code | LC1F |
| Control Circuit Type | DC standard |

Environment

| | |
|---|---|
| Ip Degree Of Protection | IP20 front face with shrouds conforming to IEC 60529 IP20 front face with shrouds conforming to VDE 0106 |
| Protective Treatment | TH |
| Ambient Air Temperature For Operation | -5...55 °C |
| Ambient Air Temperature For Storage | -60...80 °C |
| Permissible Ambient Air Temperature Around The Device | -40...70 °C |
| Height | 206 mm |
| Width | 261 mm |
| Depth | 219 mm |
| Operating Altitude | 3000 m without derating |
| Net Weight | 9.5 kg |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 25.5 cm |
| Package 1 Width | 23.5 cm |
| Package 1 Length | 29.0 cm |

| | |
|------------------|--------|
| Package 1 Weight | 9.4 kg |
|------------------|--------|

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

| | |
|---------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov |